FL1-H3777NN2-2220N



FL1000 Fiber Wall Box, 2-door, singlemode SC/UPC, 24-ports, with pigtails and splice tray, 2 cable clamps, 2 compression fittings, 2 grounding kits

- · Ideal for small to medium fiber counts within communication rooms or closets at customer sites
- Provides demarcation access for the telecom carrier and the end-user by way of separate compartments
- Guarantees mechanical protection and fiber management for indoor and outdoor cable
- Fully customizable for patch-patch, splice-patch or for the storage of un-terminated (dark) fibers

Product Classification

Regional AvailabilityNorth AmericaProduct TypeFiber wall boxProduct SeriesFL1000

General Specifications

FunctionalityPatching| SplicingApplicationPatching| Splicing

Adapter Packs Included, quantity 2

Adapters, quantity 24

Cable Clamps, quantity 2

Cable Compression Fittings, quantity 2

Cable Entry Location Bottom left | Bottom right | Top left | Top right

Cable Type Pigtails - Stranded

Color Putty white

Door, quantity 2

Front Door Type Single hinged
Growth Configuration Fully loaded
Interface SC/UPC
Mounting Wall

Splicing Type Heat shrink, mass fusion

Total Fibers, quantity 24

Total Ports, quantity 24

COMMSCOPE®

FL1-H3777NN2-2220N


Dimensions

 Height
 590 mm | 23.228 in

 Width
 551 mm | 21.693 in

 Depth
 156.97 mm | 6.18 in

Outline Drawing



Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Environmental Space Indoor

Qualification Standards NEMA type 12

Packaging and Weights

Included Two grounding kits

Page 2 of 3

FL1-H3777NN2-2220N

Packaging quantity 1

Packaging Type Bag | Carton

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

