



MPOptimate® Universal Connectivity Platform (UCP) Q-Fit Module, MPO to LC-quad, OM4, 12F pair straight

OBSOLETE

This product was discontinued on: June 28, 2019

Replaced By:

760242495

DM12-24LC-LS-A

G2 MPOptimate® Multimode OM4 MPO-12 Distribution Module, 2x12F MPO pinned to 24F LC Aqua with internal shutters, Method A Pair Straight

Product Classification

Regional Availability	Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber module
Product Brand	MPOptimate®
Product Series	UCP

General Specifications

Application	For use with Universal Connectivity Product (UCP) panels
Adapter Color	Aqua
Adapters, quantity, front	3
Adapters, quantity, rear	1
Body Style	Quad Straight orientation
Color, front	Black
Color, housing	Black
Color, rear	Black
Interface, front	LC
Interface Feature, front	Standard
Interface, rear	MPO

1671227-5

Interface Feature, rear	Standard
Polarity	Pairs, straight
Total Ports, quantity, front	12

Optical Specifications

Fiber Mode	Multimode
Fiber Type	OM4

Packaging and Weights

Packaging quantity	1
Packaging Type	Bag Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted

