

Passive Optical LAN-PON Fiber Splitter Adapter Plate with splitter, 1 x 32

Product Classification

 Regional Availability
 North America

 Portfolio
 CommScope®

 Product Type
 Splitter module

Product Series OLS

General Specifications

Device Type Plug-and-play module

Functionality Splitting
Access Front
Circuits, quantity 1

Distribution Type 1 x 32 splitter

 Interface, front
 SC/APC

 Interface, Input
 SC/APC

 Interface, Output
 SC/APC

 Interface, rear
 SC/APC

Split Ratio Symmetrical

Splitter, quantity 1

Optical Specifications

Directivity, minimum60 dBPolarization Dependent Loss, maximum0.3 dBUniformity, maximum1.3 dB

Wavelength Range 1260–1635 nm

Insertion Loss, Splitter, maximum16.7 dBInsertion Loss, Splitter, typical16 dBReturn Loss, Splitter, minimum55 dB

COMMSCOPE®

2111684-1

Environmental Specifications

Operating Temperature $-55 \,^{\circ}\text{C} \text{ to } +85 \,^{\circ}\text{C} \, (-67 \,^{\circ}\text{F to } +185 \,^{\circ}\text{F})$

Qualification Standards Telcordia GR-1209-CORE | Telcordia GR-1221-CORE

Packaging and Weights

Included Adapter plate

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

