

Angled Panel Cover, Black



Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Cover

General Specifications

Application	For angled panel
Color	Black
Rack Type	EIA 19 in

Dimensions

Height	2.286 mm 0.09 in
Width	328.676 mm 12.94 in
Depth	97.028 mm 3.82 in

Material Specifications

Material Type	Powder-coated steel
---------------	---------------------

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	Up to 95%, non-condensing
Flammability Rating	UL 94 V-0
Safety Standard	UL cUL

Packaging and Weights

Packaging Material Eco-friendly, single-use plastics-free

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

