



## SYSTIMAX 360™ Evolve M Series Bezel, 4 Package

### Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	SYSTIMAX®
<b>Product Type</b>	Bezel
<b>Product Brand</b>	SYSTIMAX 360™

### General Specifications

<b>ANSI/TIA Category</b>	5e   6   6A
<b>Cable Type</b>	U/UTP (unshielded)
<b>Color</b>	Cool gray
<b>Total Ports, quantity</b>	6

### Dimensions

<b>Height</b>	43.434 mm   1.71 in
<b>Width</b>	106.68 mm   4.2 in
<b>Depth</b>	20.066 mm   0.79 in

### Material Specifications

<b>Material Type</b>	High-impact, flame retardant, thermoplastic   Powder-coated steel
----------------------	---

### Environmental Specifications

<b>Operating Temperature</b>	-10 °C to +60 °C (+14 °F to +140 °F)
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Relative Humidity</b>	Up to 95%, non-condensing
<b>Flammability Rating</b>	UL 94 V-0
<b>Safety Standard</b>	UL   cUL

### Packaging and Weights

# 760187179 | 360-E-MOD-B-KIT

---

**Packaging quantity** 4  
**Weight, net** 0.059 kg | 0.13 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

