



SYSTIMAX 360™ Evolve M Series Bezel, 4 Package

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	SYSTIMAX®
Product Type	Bezel
Product Brand	SYSTIMAX 360™

General Specifications

ANSI/TIA Category	5e 6 6A
Cable Type	U/UTP (unshielded)
Color	Cool gray
Total Ports, quantity	6

Dimensions

Height	43.434 mm 1.71 in
Width	106.68 mm 4.2 in
Depth	20.066 mm 0.79 in

Material Specifications

Material Type	High-impact, flame retardant, thermoplastic Powder-coated steel
----------------------	---

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	Up to 95%, non-condensing
Flammability Rating	UL 94 V-0
Safety Standard	UL cUL

Packaging and Weights

Packaging quantity 4

Weight, net 0.059 kg | 0.13 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

