760227314 | UD-4U



Ultra High Density 4U modular cassette sliding Panel, accepts (24) G2 modules or MPO panels, providing up to 288 duplex LC ports or up to 192 MPO ports

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Fiber patch panel

Product Series UD

General Specifications

Application Accepts twenty-four G2 modular cassettes

Color Gray

Intelligence Type iPatch® ready

Interface, front Unloaded

Rack Units 4

Shelf Movement Sliding

Total Ports, quantity 0

Dimensions

 Height
 177.8 mm | 7 in

 Width
 482.6 mm | 19 in

 Depth
 553.97 mm | 21.81 in

Material Specifications

Material Type Acrylonitrile butadiene styrene (ABS) | Polycarbonate (PC) | Steel

Environmental Specifications

Flammability Rating UL 94 V-0

Packaging and Weights

Packaging quantity 1

Page 1 of 2

760227314 | UD-4U

Weight, net 15.966 kg | 35.2 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

