

760231498 | SD-4U-FX



Standard Density 4U fixed Panel, accepts (12) LGX/1000 style footprint modules or panels, providing up to 144 duplex LC ports

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch panel
Product Series	SD

General Specifications

Application	Accepts twelve LGX/1000 footprint panels/cassettes
Color	Black
Rack Units	4
Shelf Movement	Fixed

Dimensions

Height	177.8 mm 7 in
Width	482.6 mm 19 in
Depth	485.14 mm 19.1 in

Material Specifications

Material Type	Acrylonitrile butadiene styrene (ABS) Polycarbonate (PC) Steel
----------------------	--

Environmental Specifications

Flammability Rating	UL 94 V-0
----------------------------	-----------

Packaging and Weights

Packaging quantity	1
---------------------------	---

760231498 | SD-4U-FX

Weight, net

9.299 kg | 20.5 lb

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

