

760236365 | UD-iP-2U-288F-LC-DM-TS-SD



UD iPATCH 2U 288F-LC Distribution Module, Tera Speed, Sliding Panel

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch/splice panel
Product Brand	iPatch® imVision®
Product Series	IPATCH UD

General Specifications

Color	Gray
Intelligence Type	iPatch® enabled
Interface, front	LC/UPC
Rack Units	2
Shelf Movement	Sliding
Total Ports, quantity	144

Dimensions

Height	88.9 mm 3.5 in
Width	482.6 mm 19 in
Depth	539.75 mm 21.25 in

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted

760236365 | UD-iP-2U-288F-LC-DM-TS-SD

UK-ROHS

Compliant/Exempted

