

MST, Fiber Optic Multiport Service Terminal, 4-port, long 2xN port, locatable flat loose tube cable stub, unterminated, 400 ft

- Hardened connectors are factory-terminated and environmentally sealed for use in optical drop cable deployments
- Plug and play adapter ports ensure rapid cable installment in the outside plant access section of the network
- Multiport Service Terminals incorporate hardened connector technology that is designed to withstand the rugged outside plant environment

Alternative products available:

HST. B4HNB0400NN000 HST, NOVUX™ Standard Terminal, 4-port, Flat toneable loose tube cable, 400 ft/121 m

Product Classification

Regional Availability

Asia | Latin America | North America

Product Type Access terminal, without splitter/tap

Product Series MST

General Specifications

Cable Type Locatable - Flat - Loose Tube

Cable, quantity

Distribution Type4 portsEnclosure ColorBlack

Mounting Handhole | Pedestal | Pole | Strand

Port Type Hardened full-size SC/APC

Port, quantity 4
Splitter, quantity 0

Stub Type Stub tail

Dimensions

 Height
 282.4 mm | 11.118 in

 Width
 129.5 mm | 5.098 in

 Depth
 84.1 mm | 3.311 in




Cable Length, stub

400 ft (121 m)


Cable Outer Diameter

5.0 mm (0.20 in)

Dimension Drawing



Ordering Tree



Material Specifications

Enclosure Material Type

Gasketed hardened plastic

COMMSCOPE®

Optical Specifications

Fiber Type G.657.A1/A2

Operating Wavelength Range 1260 – 1635 nm

Attenuation Cable Coefficient, maximum 0.30 dB/km @ 1550 nm | 0.40 dB/km @ 1310 nm

Attenuation Terminal Connectors, maximum0.4 dBDirectivity, minimum60 dBInsertion Loss, Terminal Connector, typical0.16 dB

Return Loss, Connector, minimum 65 dB

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Relative Humidity 5%–100%, condensing

Environmental Space Above ground | Below ground | Buried

Flammability Rating UL 94 5VA

Qualification Standards | Telcordia GR-3120-CORE | Telcordia GR-3120-CORE | Telcordia

GR-326-CORE | Telcordia GR-771-CORE

UV Resistance UV stabilized

Packaging and Weights

Included Enclosure (1) | Universal mounting bracket (1)

Packaging quantity 1

Packaging Type Box | Carton

Weight, without cable 0.86 kg | 1.896 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant





Included Products

MST-UMB-0204 - MST, Fiber Optic Universal Mounting Bracket, 2/4 port