

NG4-VMKNLF4C010GM



NG4access® Module VAM, Monitoring, 70/30, multimode, LC/UPC, front, left, 4 circuits

- VAMs help enhance optical transport systems by providing flexible, easy to incorporate optical components into the network
- VAMs increase fiber capacity and help troubleshooting or distributing signals to multiple subscribers
- *Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Monitoring module
Product Brand	NG4access®
Product Series	NG4
Government Funding	Build America Buy America (BABA) compliant*

General Specifications

Device Type	Plug-and-play module
Functionality	Splitting
Access	Front
Application	For use with NG4 access frames
Circuits, quantity	4
Distribution Type	1 x 2 splitter
Interface, front	LC/UPC
Interface, Input	LC/UPC
Interface, Output	LC/UPC
Split Ratio	70/30
Splitter, quantity	4
Tray Orientation	Left orientation

NG4-VMKNLF4C010GM

Dimensions

Height	13.21 mm 0.52 in
Width	159.77 mm 6.29 in
Depth	130.3 mm 5.13 in

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

