## RCP-172PU706125



RapidFiber® Termination Panel, 24-Position 1RU, singlemode, dual 12fiber 3 mm plenum-rated, 61 m, 25 in breakout

#### Product Classification

**Regional Availability** Latin America | North America

**Portfolio** CommScope®

**Product Type** Fiber patch panel, with rapid cable

**Product Brand** RapidFiber®

**Product Series RCP** 

### General Specifications

**Cable Exit Location** 

Interface, rear

**Functionality** Patching

**Body Style** Symmetrical

**Cable Stub Type** Indoor, microcable

Color Putty white

Door Type, front Hinged | Slide latch | Transparant

Rear, left side

**Growth Configuration** Fully loaded Interface, front SC/UPC SC/UPC

**Patch Cord Entry Location** Front, left side | Front, right side

Rack Type EIA 19 in | EIA 23 in

**Rack Units** 1

**Shelf Movement** Sliding 24 **Total Fibers, quantity** 

**Total Ports, quantity** 24

**Transmission Standards** IEC 60794-2 | ISO/IEC 11801 | TIA/EIA-568-B.3

Dimensions

Height 44.45 mm | 1.75 in Width 482.6 mm | 19 in


**COMMSCOPE®** 

## RCP-172PU706125

**Depth** 381 mm | 15 in

**Cable Length** 61 m | 200.131 ft

### Ordering Tree



ONLY FOR MULTIMODE VERSION.1
ONLY AVAILABLE IN RISERPLENUM (P) CABLE TYPE?
RAPID PANEL IS DESIGNED AND QUALIFIED FOR UP TO 1000' (305 METERS) OF CABLE.1
ONLY AVAILABLE IN 1C288 48U<sup>4</sup>

## Material Specifications

**Finish** Powder coated

Material Type Steel

**Optical Specifications** 

Fiber Mode Singlemode

**Fiber Type** G.652.D | G.657.A2/B2

**COMMSCOPE®** 

# RCP-172PU706125

### **Environmental Specifications**

Operating Temperature  $-5 \,^{\circ}\text{C}$  to  $+55 \,^{\circ}\text{C}$  (+23  $^{\circ}\text{F}$  to +131  $^{\circ}\text{F}$ )

Storage Temperature  $-40 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  (-40  $^{\circ}\text{F}$  to +158  $^{\circ}\text{F}$ )

**Relative Humidity** 5%–85%, non-condensing

Qualification Standards NEBS Level 3 | Telcordia GR-1435 | Telcordia GR-326 | Telcordia GR-409 | UL 1863

### Packaging and Weights

Packaging quantity 1

### Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

