# RCP-47APU718325



RapidFiber® Termination Panel, 144-Position 4RU, singlemode, SC/UPC to SC/UPC, 183 m

#### **Product Classification**

Regional Availability Latin America | North America

Portfolio CommScope®

**Product Type** Fiber patch panel, with rapid cable

Product Brand RapidFiber®

Product Series RCP

## General Specifications

**Functionality** Patching

Body Style Symmetrical

Cable Exit Location Rear, left side

Cable Stub Type Indoor, microcable

**Color** Putty white

Door Type, front Hinged | Slide latch | Transparant

Growth ConfigurationFully loadedInterface, frontSC/UPC

Interface, rear SC/UPC

Patch Cord Entry Location Front, left side | Front, right side

Rack Type EIA 19 in | EIA 23 in

Rack Units 4

Shelf Movement Sliding

Total Fibers, quantity 144

Total Ports, quantity 144

**Transmission Standards** IEC 60794-2 | ISO/IEC 11801 | TIA/EIA-568-B.3

**Dimensions** 

**Height** 177.8 mm | 7 in

**COMMSCOPE®** 


# RCP-47APU718325

 Width
 482.6 mm | 19 in

 Depth
 381 mm | 15 in

**Cable Length** 183 m | 600.394 ft

### Ordering Tree



ONLY FOR MULTIMODE VERSION.<sup>1</sup>
ONLY AVAILABLE IN RISER/PLENUM (P) CABLE TYPE<sup>2</sup>
RAPID PANEL IS DESIGNED AND QUALIFIED FOR UP TO 1000' (305 METERS) OF CABLE.<sup>1</sup>
ONLY AVAIL ABLE IN IC (298 ABLE)<sup>1</sup>

## Material Specifications

**Finish** Powder coated

Material Type Steel

**Optical Specifications** 

Fiber Mode Singlemode

**Fiber Type** G.652.D | G.657.A2/B2

COMMSCOPE®

# RCP-47APU718325

#### **Environmental Specifications**

**Operating Temperature**  $-5 \,^{\circ}\text{C} \text{ to } +55 \,^{\circ}\text{C} \text{ (+23 }^{\circ}\text{F to } +131 \,^{\circ}\text{F)}$ 

**Storage Temperature**  $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$ 

**Relative Humidity** 5%–85%, non-condensing

Qualification Standards NEBS Level 3 | Telcordia GR-1435 | Telcordia GR-326 | Telcordia GR-409 | UL 1863

#### Packaging and Weights

Packaging quantity

## Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

