


RCP-C1K4PUJ03100



RapidFiber® Termination Panel, 48-Position 1RU, singlemode, LC/UPC to SC/APC, spool, 31 m

Product Classification

| | |
|------------------------------|-------------------------------------|
| Regional Availability | Latin America North America |
| Portfolio | CommScope® |
| Product Type | Fiber patch panel, with rapid cable |
| Product Brand | RapidFiber® |
| Product Series | RCP |

General Specifications

| | |
|----------------------------------|---|
| Functionality | Patching |
| Body Style | Symmetrical |
| Cable Exit Location | Rear, left side |
| Cable Stub Type | Indoor, microcable |
| Color | Putty white |
| Door Type, front | Hinged Slide latch Transparent |
| Growth Configuration | Fully loaded |
| Interface, front | LC/UPC |
| Interface, rear | SC/APC |
| Patch Cord Entry Location | Front, left side Front, right side |
| Rack Type | EIA 19 in EIA 23 in |
| Rack Units | 1 |
| Shelf Movement | Sliding |
| Total Fibers, quantity | 48 |
| Total Ports, quantity | 48 |
| Transmission Standards | IEC 60794-2 ISO/IEC 11801 TIA/EIA-568-B.3 |


Dimensions

| | |
|---------------|--------------------|
| Height | 44.45 mm 1.75 in |
| Width | 482.6 mm 19 in |

RCP-C1K4PUJ03100

Depth 381 mm | 15 in
Cable Length 31 m | 101.706 ft

Ordering Tree



Material Specifications

Finish Powder coated
Material Type Steel

Optical Specifications

Fiber Mode Singlemode
Fiber Type G.652.D | G.657.A2/B2

RCP-C1K4PUJ03100

Environmental Specifications

| | |
|--------------------------------|--|
| Operating Temperature | -5 °C to +55 °C (+23 °F to +131 °F) |
| Storage Temperature | -40 °C to +70 °C (-40 °F to +158 °F) |
| Relative Humidity | 5%–85%, non-condensing |
| Qualification Standards | NEBS Level 3 Telcordia GR-1435 Telcordia GR-326 Telcordia GR-409 UL 1863 |

Packaging and Weights

| | |
|---------------------------|---|
| Packaging quantity | 1 |
|---------------------------|---|

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|-----------------------------------|
| CHINA-ROHS | Above maximum concentration value |
| ROHS | Compliant/Exempted |
| UK-ROHS | Compliant/Exempted |

