TFP-1TAQ2-010B

TFP Fiber Termination Panel, 48 LC/UPC, multimode, 1RU, 19 in, black

Product Classification

Regional Availability Latin America | North America

Portfolio CommScope®
Product Type Fiber patch panel

Product Series TFP

General Specifications

Functionality Patching | Splicing

Body Style Symmetrical

ColorBlackColor, frontBlackInterface, frontLC/UPC

Patch Cord Entry Location Front, left side | Front, right side

Rack Type EIA 19 in | EIA 23 in

Rack Units 1

Shelf Movement Sliding

Total Ports, quantity 48

Dimensions

 Height
 44.45 mm | 1.75 in


 Width
 482.6 mm | 19 in

 Depth
 399.29 mm | 15.72 in

Ordering Tree



TFP-1TAQ2-010B



Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Multimode

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F}$)

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F}$)

Packaging and Weights

Included Mounting hardware

Packaging quantity 1

Weight, net 4.649 kg | 10.25 lb

Regulatory Compliance/Certifications



TFP-1TAQ2-010B

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

