



Patch Panel, category 6, 24-port, 1 RU, RJ45, universal T568A/B wiring, black

**OBSOLETE**

This product was discontinued on: October 1, 2018

**Replaced By:**

760237040 CPP-UDDM-SL-1U-24	Discrete Distribution Module Panel, SL, UTP, 1U, 24 port
9-1375055-2	SL110 Series Modular Jack, RJ45, category 6, T568A/T568B, unshielded, without dust cover, bag of 24, black

Product Classification

Regional Availability	Australia/New Zealand
Portfolio	NETCONNECT®
Product Type	RJ45 patch panel

General Specifications

ANSI/TIA Category	6
Color	Black
Growth Configuration	Fully loaded
Interface, front	RJ45 jack
Panel Mounting	Flush
Panel Style	Straight
Rack Type	EIA 19 in
Rack Units	1
Termination Type	IDC
Total Ports, quantity	24
Transmission Standards	ANSI/TIA-568-C.2   ISO/IEC 11801 Class E
Wiring	T568A   T568B

Dimensions

# 1933796-2

---

Height	44.45 mm   1.75 in
Width	482.6 mm   19 in

## Material Specifications

Material Type	High-impact, flame retardant, thermoplastic   Steel
---------------	---

## Packaging and Weights

Packaging quantity	1
Packaging Type	Bag   Box

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

