

Patch Panel, category 6, 24-port, 1 RU, RJ45, universal T568A/B wiring, black



OBSOLETE

This product was discontinued on: October 1, 2018

Replaced By:

760237040 CPP-UDDM-SL-1U-24	Discrete Distribution Module Panel, SL, UTP, 1U, 24 port
9-1375055-2	SL110 Series Modular Jack, RJ45, category 6, T568A/T568B, unshielded, without dust cover, bag of 24, black

Product Classification

Regional Availability	Australia/New Zealand
Portfolio	NETCONNECT®
Product Type	RJ45 patch panel

General Specifications

ANSI/TIA Category	6
Color	Black
Growth Configuration	Fully loaded
Interface, front	RJ45 jack
Panel Mounting	Flush
Panel Style	Straight
Rack Type	EIA 19 in
Rack Units	1
Termination Type	IDC
Total Ports, quantity	24
Transmission Standards	ANSI/TIA-568-C.2 ISO/IEC 11801 Class E

1933796-2

Wiring T568A | T568B

Dimensions

Height 44.45 mm | 1.75 in

Width 482.6 mm | 19 in

Material Specifications

Material Type High-impact, flame retardant, thermoplastic | Steel

Packaging and Weights

Packaging quantity 1

Packaging Type Bag | Box

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

REACH-SVHC

ROHS

Classification

Below maximum concentration value

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

