



iPatch® M4200i 24 Port UTP Intelligent Universal Modular Panel without Modules

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	SYSTIMAX®
Product Type	RJ45 patch panel
Product Brand	iPatch® imVision®

General Specifications

ANSI/TIA Category	6 6A
Cable Type	Unshielded
Color	Black
Intelligence Type	iPatch® enabled
Panel Style	Straight
Rack Units	1
Total Ports, quantity	24

Dimensions

Height	44.45 mm 1.75 in
Width	482.6 mm 19 in
Depth	25.4 mm 1 in

Material Specifications

Material Type	Acrylonitrile butadiene styrene (ABS) Polycarbonate
----------------------	---

Environmental Specifications

Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	Up to 95%, non-condensing
Flammability Rating	UL 94 V-0
Safety Standard	ACMA CE UL cUL

Packaging and Weights

Included	Cable management bar Four #12-24 dog point mounting screws Information outlet removal tool Instruction sheet Panel Two #12 washers Two #12-24 screws
Packaging quantity	1
Weight, net	0.68 kg 1.5 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted

