

760104307 | M4800-1U-PS



M4800 1U Modular Panel, 48 port (MPS100 / UNJ10G / UNJ600 / UNJ600T / UNJ500), Black

- Available for use with the DYMO® labeling solution

This product will be discontinued on: January 31, 2025

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | CommScope® |
| Product Type | RJ45 patch panel |
| Product Series | M Series |

General Specifications

| | |
|------------------------------|-----------|
| ANSI/TIA Category | 5e 6 |
| Color | Black |
| Intelligence Type | Passive |
| Rack Type | EIA 19 in |
| Rack Units | 1 |
| Total Ports, quantity | 48 |

Dimensions

| | |
|---------------|--------------------|
| Height | 44.45 mm 1.75 in |
| Width | 482.6 mm 19 in |
| Depth | 53.85 mm 2.12 in |

Material Specifications

| | |
|----------------------|---|
| Material Type | High-impact, flame retardant, thermoplastic Steel |
|----------------------|---|

Environmental Specifications

| | |
|------------------------------|--------------------------------------|
| Operating Temperature | -10 °C to +60 °C (+14 °F to +140 °F) |
| Storage Temperature | -40 °C to +70 °C (-40 °F to +158 °F) |

760104307 | M4800-1U-PS

| | |
|----------------------------|---------------------------|
| Relative Humidity | Up to 95%, non-condensing |
| Flammability Rating | UL 94 V-0 |
| Safety Standard | UL cUL |

Packaging and Weights

| | |
|---------------------------|--|
| Packaging Material | Eco-friendly, single-use plastics-free |
| Packaging quantity | 1 |

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Below maximum concentration value |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

