# 760184507 | FLEXIMAX

#### Unshielded Modular Panel, M-series, 1U, 24 port, Black



#### **Product Classification**

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®
Product Type RJ45 patch panel

**Product Series** M Series

## General Specifications

Cable Type Unshielded

Color Black
Intelligence Type Passive
Rack Type EIA 19 in

Rack Units 1

Total Ports, quantity 24

#### Dimensions

 Height
 43.69 mm | 1.72 in

 Width
 482.6 mm | 19 in

 Depth
 105.92 mm | 4.17 in

## Material Specifications

Material Type High-impact, flame retardant, thermoplastic | Powder-coated steel

# **Environmental Specifications**

Operating Temperature  $-10 \,^{\circ}\text{C}$  to  $+60 \,^{\circ}\text{C}$  (+14  $^{\circ}\text{F}$  to +140  $^{\circ}\text{F}$ )

Storage Temperature  $-40 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  (-40  $^{\circ}\text{F}$  to +158  $^{\circ}\text{F}$ )

Page 1 of 2

# 760184507 | FLEXIMAX

Safety Standard UL | cUL

Packaging and Weights

 Packaging Material
 Eco-friendly, single-use plastics-free

Packaging quantity 1

### Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

