



SYSTIMAX 360™ Evolve 24-port flat panel

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	SYSTIMAX®
Product Type	RJ45 patch panel
Product Brand	SYSTIMAX 360™
Product Series	M Series

General Specifications

Cable Type	Unshielded
Color	Cool gray
Modules, quantity	24
Panel Style	Straight
Rack Type	EIA 19 in
Rack Units	1
Total Ports, quantity	24
Wiring	T568A T568B

Dimensions

Height	44.45 mm 1.75 in
Label Height	10.922 mm 0.43 in
Width	482.6 mm 19 in
Depth	40.64 mm 1.6 in
Depth, with cable management	170.18 mm 6.7 in
Label Length	33.782 mm 1.33 in
Compatible Diameter Over Dielectric, maximum	1.168 mm 0.046 in
Compatible Diameter Over Dielectric, minimum	0.762 mm 0.03 in

760187187 | 360-E-MOD-1U-24

Electrical Specifications

Current Rating at Temperature	1.5 A @ 20 °C 1.5 A @ 68 °F
Dielectric Withstand Voltage, RMS, conductive surface	1,500 Vac @ 60 Hz
Dielectric Withstand Voltage, RMS, contact-to-contact	1,000 Vac @ 60 Hz
Insulation Resistance, minimum	500 MOhm

Material Specifications

Material Type	High-impact, flame retardant, thermoplastic Powder-coated steel
----------------------	---

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	Up to 95%, non-condensing
Flammability Rating	UL 94 V-0
Safety Standard	UL cUL

Packaging and Weights

Packaging Material	Eco-friendly, single-use plastics-free Eco-friendly, single-use plastics-free
Packaging quantity	1
Weight, net	0.499 kg 1.1 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

