



SYSTIMAX 360™ Evolve 48-port flat panel

Product Classification

|                       |   |
|-----------------------|---|
| Regional Availability | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| Portfolio             | SYSTIMAX®   |
| Product Type          | RJ45 patch panel  |
| Product Brand         | SYSTIMAX 360™   |
| Product Series        | M Series  |

General Specifications

|                       |               |
|-----------------------|---------------|
| Cable Type            | Unshielded    |
| Color                 | Cool gray     |
| Modules, quantity     | 48            |
| Panel Style           | Straight      |
| Rack Type             | EIA 19 in     |
| Rack Units            | 2             |
| Total Ports, quantity | 48            |
| Wiring                | T568A   T568B |

Dimensions

|  |                     |
|--|---------------------|
| Height                                       | 88.9 mm   3.5 in    |
| Label Height                                 | 10.922 mm   0.43 in |
| Width  | 482.6 mm   19 in    |
| Depth  | 43.18 mm   1.7 in   |
| Depth, with cable management                 | 172.72 mm   6.8 in  |
| Label Length                                 | 33.782 mm   1.33 in |
| Compatible Diameter Over Dielectric, maximum | 1.168 mm   0.046 in |
| Compatible Diameter Over Dielectric, minimum | 0.762 mm   0.03 in  |

# 760187195 | 360-E-MOD-2U-48

## Electrical Specifications

|   |                               |
|---|-------------------------------|
| Current Rating at Temperature                         | 1.5 A @ 20 °C   1.5 A @ 68 °F |
| Dielectric Withstand Voltage, RMS, conductive surface | 1,500 Vac @ 60 Hz             |
| Dielectric Withstand Voltage, RMS, contact-to-contact | 1,000 Vac @ 60 Hz             |
| Insulation Resistance, minimum                        | 500 MOhm                      |

## Material Specifications

|               |   |
|---------------|---|
| Material Type | High-impact, flame retardant, thermoplastic   Powder-coated steel |
|---------------|---|

## Environmental Specifications

|                       |                                      |
|-----------------------|--------------------------------------|
| Operating Temperature | -10 °C to +60 °C (+14 °F to +140 °F) |
| Storage Temperature   | -40 °C to +70 °C (-40 °F to +158 °F) |
| Relative Humidity     | Up to 95%, non-condensing            |
| Flammability Rating   | UL 94 V-0                            |
| Safety Standard       | UL   cUL                             |

## Packaging and Weights

|                    |                   |
|--------------------|-------------------|
| Packaging quantity | 1                 |
| Weight, net        | 1.043 kg   2.3 lb |

## Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| CHINA-ROHS    | Below maximum concentration value  |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system   |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant  |
| UK-ROHS       | Compliant  |

