



SYSTIMAX 360™ Evolve 48-port angled panel

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio

SYSTIMAX®

Product Type

RJ45 patch panel

Product Brand

SYSTIMAX 360™

Product Series

M Series

General Specifications

Cable Type

Unshielded

Color

Cool gray

Modules, quantity

48

Panel Style

Angled

Rack Type

EIA 19 in

Rack Units

2

Total Ports, quantity

48

Wiring

T568A | T568B

Dimensions

Height

88.9 mm | 3.5 in

Label Height

10.922 mm | 0.43 in

Width

482.6 mm | 19 in

Depth

142.24 mm | 5.6 in

Depth, with cable management

271.78 mm | 10.7 in

Label Length

33.782 mm | 1.33 in

Compatible Diameter Over Dielectric, maximum

1.168 mm | 0.046 in

Compatible Diameter Over Dielectric, minimum

0.762 mm | 0.03 in

760187211 | 360-E-ANG-MOD-2U-48

Electrical Specifications

Current Rating at Temperature	1.5 A @ 20 °C 1.5 A @ 68 °F
Dielectric Withstand Voltage, RMS, conductive surface	1,500 Vac @ 60 Hz
Dielectric Withstand Voltage, RMS, contact-to-contact	1,000 Vac @ 60 Hz
Insulation Resistance, minimum	500 MOhm

Material Specifications

Material Type	High-impact, flame retardant, thermoplastic Powder-coated steel
----------------------	---

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	Up to 95%, non-condensing
Flammability Rating	UL 94 V-0
Safety Standard	UL cUL

Packaging and Weights

Packaging Material	Eco-friendly, single-use plastics-free
Packaging quantity	1
Weight, net	1.089 kg 2.4 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

