



1100 GS6 PANEL KIT - 2U

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio

SYSTIMAX®

Product Type

RJ45 patch panel

General Specifications

ANSI/TIA Category

6A

Cable Type

Unshielded

Color

Black

Modules, quantity

8

Panel Style

Straight

Rack Type

EIA 19 in

Rack Units

2

Total Ports, quantity

48

Dimensions

Height

88.9 mm | 3.5 in

Width

482.6 mm | 19 in

Depth

119.38 mm | 4.7 in

Electrical Specifications

Current Rating at Temperature

1.5 A @ 20 °C | 1.5 A @ 68 °F

Dielectric Withstand Voltage, RMS, conductive surface

1,500 Vac @ 60 Hz

Dielectric Withstand Voltage, RMS, contact-to-contact

1,000 Vac @ 60 Hz

Material Specifications

Material Type

Powder-coated steel

Mechanical Specifications

760206953 | 1100-U-GS6-KIT-2U

Plug Insertion Life, test plug

IEC 60603-7 compliant plug

Environmental Specifications

Operating Temperature

-10 °C to +60 °C (+14 °F to +140 °F)

Storage Temperature

-40 °C to +70 °C (-40 °F to +158 °F)

Relative Humidity

Up to 95%, non-condensing

Flammability Rating

UL 94 V-0

Safety Standard

UL | cUL

Packaging and Weights

Packaging quantity

1

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

