



G2 LL Multimode OM5 MPO 12 distribution module, 24 LC to 2x12f MPO's pinned, internal shutters

## Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Fiber module
Product Brand	InstaPATCH® 360
Product Series	G2

## General Specifications

Functionality	Breakout
Color, front	Lime green
Color, rear	Gray
Interface, front	LC/UPC
Interface, rear	MPO
Interface Feature, rear	Key up/up   Pinned
Polarity	Method B
Shuttered	Yes
Total Fibers, quantity	24

## Dimensions

Height	25.51 mm   1.004 in
Width	95.91 mm   3.776 in
Depth	119.69 mm   4.712 in

## Optical Specifications

Fiber Mode	Multimode
Fiber Type	OM5
Insertion Loss, maximum	0.47 dB

Environmental Specifications

Qualification Standards	IEC 61753-1   TIA-568.3-D
Safety Standard	CE   CSA   UL

Packaging and Weights

Packaging quantity	1
Weight, net	0.109 kg   0.24 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

