



Shielded Discrete Distribution Module, SL, (4 ea/pkg), Black

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Module

## General Specifications

<b>Color</b>	Black
--------------	-------

## Dimensions

<b>Height</b>	41.148 mm   1.62 in
<b>Width</b>	106.68 mm   4.2 in
<b>Depth</b>	32.512 mm   1.28 in

## Material Specifications

<b>Material Type</b>	High-impact, flame retardant, thermoplastic
----------------------	---

## Environmental Specifications

<b>Operating Temperature</b>	-10 °C to +60 °C (+14 °F to +140 °F)
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Relative Humidity</b>	Up to 95%, non-condensing
<b>Flammability Rating</b>	UL 94 V-0
<b>Safety Standard</b>	UL   cUL

## Packaging and Weights

<b>Packaging quantity</b>	4
---------------------------	---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
---------------	-----------------------

# 760238661 | CPP-SDDM-SL-KIT-4PK

---

CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

