

# 760238951 | FD-8-1U-A



1RU patch panel which interfaces with QSFP ports to easily break them out in LC connections. The MPO and LC ports are both front facing for easy mapping and patching. 10 singlemode MPO-8 and 40 duplex shuttered LC ports, Method A

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber patch panel
<b>Product Series</b>	FD

## General Specifications

<b>Color</b>	Black
<b>Interface, front</b>	LC/UPC   MPO
<b>Rack Units</b>	1
<b>Shelf Movement</b>	Fixed
<b>Total Ports, quantity</b>	90

## Dimensions

<b>Height</b>	44.45 mm   1.75 in
<b>Width</b>	482.6 mm   19 in
<b>Depth</b>	292.1 mm   11.5 in

## Optical Specifications

<b>Insertion Loss, maximum</b>	0.6 dB
--------------------------------	--------

## Environmental Specifications

<b>Safety Standard</b>	UL 60950
------------------------	----------

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

