



UDS 6RU splice panel, 432 duplex LC/APC ports, Enhanced Method B

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber patch/splice panel
<b>Product Series</b>	UDS

## General Specifications

<b>Application</b>	Preloaded with 36 UDS modules
<b>Color</b>	White
<b>Intelligence Type</b>	Not iPatch® ready
<b>Interface, front</b>	LC/APC
<b>Pigtail Assembly Type</b>	12-fiber, ribbon
<b>Pigtails Included, quantity</b>	36
<b>Rack Type</b>	EIA 19 in
<b>Rack Units</b>	6
<b>Shelf Movement</b>	Sliding
<b>Splice Trays Included, quantity</b>	12
<b>Total Ports, quantity</b>	432

## Dimensions

<b>Height</b>	266.7 mm   10.5 in
<b>Width</b>	444.5 mm   17.5 in
<b>Depth</b>	609.6 mm   24 in

## Optical Specifications

<b>Insertion Loss, maximum</b>	0.4 dB
--------------------------------	--------

## Environmental Specifications

**Safety Standard** cUL US 1863

## Packaging and Weights

**Packaging quantity** 1

**Weight, net** 20.412 kg | 45 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

