

760239074 | UDS-2U-BK-LC-A-ULL



UDS 2RU splice panel, 144 duplex LC/UPC ports, Method A

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch/splice panel
Product Series	UDS

General Specifications

Application	Preloaded with 12 UDS modules
Color	Black
Intelligence Type	Not iPatch® ready
Interface, front	LC/UPC
Pigtail Assembly Type	12-fiber, ribbon
Pigtails Included, quantity	12
Rack Type	EIA 19 in
Rack Units	2
Shelf Movement	Sliding
Splice Trays Included, quantity	4
Total Ports, quantity	144

Dimensions

Height	88.9 mm 3.5 in
Width	444.5 mm 17.5 in
Depth	609.6 mm 24 in

Optical Specifications

Insertion Loss, maximum	0.25 dB
--------------------------------	---------

Environmental Specifications

Safety Standard cUL US 1863

Packaging and Weights

Packaging quantity 1

Weight, net 6.804 kg | 15 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant

