760239962 | FACT-2ESPLA04



FACT® Fiber Optic Splice Chassis, gray, 2E high, loaded with 24 trays for holding up to 4 ANT type splices per tray

- Designed for use with the all-purpose all-front-access FACT frames and FIST-GR3 frames supporting up to 2,688 LC or 1,344 SC connections in a single frame (FACT-IC frame 2880 LC or 1440 SC)
- Reduced installation and maintenance time via the toolless snap-on design supporting both interconnect and cross-connect applications
- Flexible customization enabled by 4 chassis types (patch-only, patch-splice, pre-cabled and splice-only) to support all ODF applications
- High density through the single FACT element height (1E) being 30% less tall compared to the industry standard panel height (1HU)

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Fiber splice chassis

Product Brand FACT®
Product Series FACT

General Specifications

Functionality Splicing

Application Compatible with FIST-GR3-style frames

Body Style Symmetrical

Color Gray

Growth ConfigurationFully loadedInterface, frontUnloadedRack TypeEIA 19 in

Rack Units 1.4

Shelf Movement Sliding

Splicing Capacity, maximum 96

Splicing Type ANT

Total Ports, quantity 0

Transmission Standards ETSI EN 300 019-1-3 | IEC 61300-3-30

COMMSCOPE®

760239962 | FACT-2ESPLA04


Dimensions

 Height
 61.9 mm | 2.437 in

 Width
 524 mm | 20.63 in

 Depth
 283 mm | 11.142 in

Ordering Tree



Environmental Specifications

Operating Temperature $-40 \, ^{\circ}\text{C} \text{ to } +70 \, ^{\circ}\text{C} \text{ (-40 } ^{\circ}\text{F to } +158 \, ^{\circ}\text{F)}$

Storage Temperature -20 °C to +85 °C (-4 °F to +176 °F)

Flammability Rating UL 94 V-0

Packaging and Weights

Included Mounting hardware for FACT frame

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant/Exempted

