## 760239971 | FACT-4ESPLA04



FACT® Fiber Optic Splice Chassis, gray, 4E high, loaded with 48 trays for holding up to 4 ANT type splices per tray

- Designed for use with the all-purpose all-front-access FACT frames and FIST-GR3 frames supporting up to 2,688 LC or 1,344 SC connections in a single frame (FACT-IC frame 2880 LC or 1440 SC)
- Reduced installation and maintenance time via the toolless snap-on design supporting both interconnect and cross-connect applications
- Flexible customization enabled by 4 chassis types (patch-only, patch-splice, pre-cabled and splice-only) to support all ODF applications
- High density through the single FACT element height (1E) being 30% less tall compared to the industry standard panel height (1HU)

#### Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

**Product Type** Fiber splice chassis

Product Brand FACT®
Product Series FACT

#### General Specifications

**Functionality** Splicing

**Application** Compatible with FIST-GR3-style frames

**Body Style** Symmetrical

**Color** Gray

Growth ConfigurationFully loadedInterface, frontUnloadedRack TypeEIA 19 in

Rack Units 2.8

Shelf Movement Sliding

Splicing Capacity, maximum 192

Splicing Type ANT

Total Ports, quantity 0

**Transmission Standards** ETSI EN 300 019-1-3 | IEC 61300-3-30



# 760239971 | FACT-4ESPLA04

#### Dimensions

 Height
 123.8 mm | 4.874 in


 Width
 524 mm | 20.63 in

 Depth
 283 mm | 11.142 in

### Splicing Configuration

NUMBER OF TRAYS PER FACT-CHASSIS				
	A04	S04	A12	S12
1E	12	12	8	6
2E	24	24	16	12
3E	36	36	24	18
4E	48	48	32	24

#### Ordering Tree



#### **Environmental Specifications**

**Operating Temperature** -40 °C to +70 °C (-40 °F to +158 °F)

Storage Temperature -20 °C to +85 °C (-4 °F to +176 °F)

Flammability Rating UL 94 V-0

## Packaging and Weights

**Included** Mounting hardware for FACT frame

Packaging quantity 1

#### Regulatory Compliance/Certifications

Agency Classification

**COMMSCOPE®** 

# 760239971 | FACT-4ESPLA04

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

