760240057 | FACT-4ERHPL4S



FACT® Fiber Optic Patch/Splice Chassis, gray, 4E high, 192-port, multimode, OM4, loaded with LC/UPC adapters and pigtails, SMOUV splice tray type, right-hand patch

- Designed for use with the all-purpose all-front-access FACT frames and FIST-GR3 frames supporting up to 2,688 LC or 1,344 SC connections in a single frame (FACT-IC frame 2880 LC or 1440 SC)
- Reduced installation and maintenance time via the toolless snap-on design supporting both interconnect and cross-connect applications
- Flexible customization enabled by 4 chassis types (patch-only, patch-splice, pre-cabled and splice-only) to support all ODF applications
- High density through the single FACT element height (1E) being 30% less tall compared to the industry standard panel height (1HU)

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Fiber patch/splice chassis

Product Brand FACT®
Product Series FACT

General Specifications

Functionality Patching | Splicing

Application Compatible with FIST-GR3-style frames

Body Style Right-hand patch

Color Gray

 Growth Configuration
 Fully loaded

 Interface, front
 LC/UPC

 Patch Cord Routing
 Right sided

Pigtail Assembly Type 12-fiber, stranded

Pigtails Included, quantity 192

Rack Type EIA 19 in

Rack Units 2.8

Shelf Movement Sliding

Splicing Capacity, maximum 192

COMMSC PE®

760240057 | FACT-4ERHPL4S

Splicing Type SMOUV

Total Ports, quantity 192

Transmission Standards ETSI EN 300 019-1-3 | IEC 61300-3-30


Dimensions

 Height
 123.8 mm | 4.874 in

 Width
 524 mm | 20.63 in

 Depth
 283 mm | 11.142 in

Ordering Tree



Optical Specifications

Fiber Mode Multimode

 Fiber Type
 OM4

 Insertion Loss, maximum
 0.5 dB

 Return Loss, minimum
 20 dB

Environmental Specifications

COMMSCOPE®

760240057 | FACT-4ERHPL4S

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+158 \,^{\circ}\text{F}$)

Storage Temperature $-20 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ (-4 $^{\circ}\text{F}$ to $+176 \,^{\circ}\text{F}$)

Flammability Rating UL 94 V-0

Packaging and Weights

Included Mounting hardware for FACT frame

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

