

FD3-AB072J1TAABP1



Enhanced Mini FDH, 72F loaded pole/wall mounted cabinet, SC/APC, preloaded w/ 1x 1:32 PNP splitter, I/O Dielectric Ribbon Cable, 100ft stubs using a 1x72F distribution cable assembly and a 1x12F feeder

Product Classification

Regional Availability	North America
Product Type	Fiber distribution hub
Product Series	FDH 3000

General Specifications

Access	Front
Cable Type	Dielectric - Ribbon
Color	Putty white
Distribution Cables, quantity	1
Distribution Ports, quantity	72
Fibers per Distribution Cable, quantity	72
Fibers per Feeder Cable, quantity	12
Interface, Input	SC
Interface Feature, Input	APC
Mounting	Pole Wall
Split Ratio	Symmetrical
Splitter Slots, quantity	8
Splitter Type	1 x 32
Splitter, quantity	1

Dimensions

Height	584.2 mm 23 in
Width	330.2 mm 13 in
Depth	203.2 mm 8 in
Cable Length	30.48 m 100 ft
Enclosure Size	Mini

FD3-AB072J1TAABP1

Material Specifications

Finish	Powder coated
Material Type	Aluminum

Environmental Specifications

Environmental Space	Above ground Aerial
Qualification Standards	Telcordia GR-3123-CORE Telcordia GR-3125-CORE

Packaging and Weights

Packaging quantity	1
Packaging Type	Pallet

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

