

# FD3-AC144J00U20P2



FDH 3000 Fiber Distribution Extra Small In-Hub Splice Cabinet, 144F, SC /APC, no splitters, loose tube pigtails, 24F

## Product Classification

Regional Availability	North America
Product Type	Fiber distribution hub
Product Series	FDH 3000

## General Specifications

Access	Front
Cable Type	Pigtails - Loose Tube
Color	Putty white
Distribution Cables, quantity	0
Distribution Ports, quantity	144
Fibers per Feeder Cable, quantity	24
Interface, Input	SC
Interface Feature, Input	APC
Mounting	Pad
Splitter Slots, quantity	9

## Dimensions

Height	914 mm   35.984 in
Width	533 mm   20.984 in
Depth	356 mm   14.016 in
Cable Length	30.48 m   100 ft
Enclosure Size	Extra small

## Material Specifications

Finish	Powder coated
Material Type	Aluminum

# FD3-AC144J00U20P2

---

## Environmental Specifications

**Environmental Space** Above ground

## Packaging and Weights

**Packaging quantity** 1

**Packaging Type** Pallet

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

