

# FD3-AE144J00TBBP4



FDH 3000 Small Fiber Distribution Cabinet, 144F, SC/APC, no splitters, dielectric ribbon, 100 ft, 48F

## Product Classification

Regional Availability	North America
Product Type	Fiber distribution hub
Product Series	FDH 3000

## General Specifications

Access	Front
Cable Type	Dielectric - Ribbon
Color	Putty white
Distribution Cables, quantity	1
Distribution Ports, quantity	288
Fibers per Distribution Cable, quantity	144
Fibers per Feeder Cable, quantity	48
Interface, Input	SC
Interface Feature, Input	APC
Mounting	Pad
Splitter Slots, quantity	12

## Dimensions

Height	914 mm   35.984 in
Width	686 mm   27.008 in
Depth	457 mm   17.992 in
Cable Length	30.48 m   100 ft
Enclosure Size	Small

## Material Specifications

Finish	Powder coated
Material Type	Aluminum

# FD3-AE144J00TBBP4

---

## Environmental Specifications

**Environmental Space** Above ground

## Packaging and Weights

**Packaging quantity** 1

**Packaging Type** Pallet

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

