

# FD3-AE144J2ATBBP2



FDH 3000 Small Fiber Distribution Cabinet, 144F, SC/APC,(2) 32-splitter modules, dielectric ribbon, 100 ft, 24F

## Product Classification

Regional Availability	North America
Product Type	Fiber distribution hub
Product Series	FDH 3000

## General Specifications

Access	Front
Cable Type	Dielectric - Ribbon
Color	Putty white
Distribution Cables, quantity	1
Distribution Ports, quantity	288
Fibers per Distribution Cable, quantity	144
Fibers per Feeder Cable, quantity	24
Interface, Input	SC
Interface Feature, Input	APC
Mounting	Pad
Split Ratio	Symmetrical
Splitter Slots, quantity	12
Splitter Type	1 x 32
Splitter, quantity	2

## Dimensions

Height	914 mm   35.984 in
Width	686 mm   27.008 in
Depth	457 mm   17.992 in
Cable Length	30.48 m   100 ft
Enclosure Size	Small

# FD3-AE144J2ATBBP2

---

## Material Specifications

Finish	Powder coated
Material Type	Aluminum

## Environmental Specifications

Environmental Space	Above ground
---------------------	--------------

## Packaging and Weights

Packaging quantity	1
Packaging Type	Pallet

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

