

# FD3-AE144J2MJBBP2



FDH 3000 Small Fiber Distribution Cabinet, 144F, SC/APC, (2) 16-splitter modules, dielectric loose tube, 100 ft, 24F

## Product Classification

Regional Availability	North America
Product Type	Fiber distribution hub
Product Series	FDH 3000

## General Specifications

Access	Front
Color	Putty white
Distribution Cables, quantity	1
Distribution Ports, quantity	144
Fibers per Distribution Cable, quantity	144
Fibers per Feeder Cable, quantity	24
Mounting	Pad
Splitter Type	1 x 16
Splitter, quantity	2

## Dimensions

Cable Length	30.48 m   100 ft
Enclosure Size	Small

## Material Specifications

Finish	Powder coated
Material Type	Aluminum

## Environmental Specifications

Environmental Space	Above ground
---------------------	--------------

## Packaging and Weights

# FD3-AE144J2MJBBP2

---

Packaging quantity	1
Packaging Type	Pallet

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

