

# FD3-AG072J00GABP2



FDH 3000 Fiber Distribution Medium Cabinet, 72F, SC/APC, no splitters, single armor loose tube, 100 ft, 24F

## Product Classification

Regional Availability	North America
Product Type	Fiber distribution hub
Product Series	FDH 3000

## General Specifications

Access	Front
Cable Type	Armored - Single Loose Tube
Color	Putty white
Distribution Cables, quantity	1
Distribution Ports, quantity	432
Fibers per Distribution Cable, quantity	72
Fibers per Feeder Cable, quantity	24
Interface, Input	SC
Interface Feature, Input	APC
Mounting	Pad
Splitter Slots, quantity	24

## Dimensions

Height	1,066.8 mm   42 in
Width	685.8 mm   27 in
Depth	457.2 mm   18 in
Cable Length	30.48 m   100 ft
Enclosure Size	Medium

## Material Specifications

Finish	Powder coated
Material Type	Aluminum

# FD3-AG072J00GABP2

---

## Environmental Specifications

**Environmental Space** Above ground

## Packaging and Weights

**Packaging quantity** 1

**Packaging Type** Pallet

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

