

FD3-AG144J00GBBP2



FDH 3000 Fiber Distribution Medium Cabinet, 144F, SC/APC, no splitters, single armor loose tube, 100 ft, 24F

Product Classification

| | |
|-----------------------|------------------------|
| Regional Availability | North America |
| Product Type | Fiber distribution hub |
| Product Series | FDH 3000 |

General Specifications

| | |
|-----------------------------------|-----------------------------|
| Access | Front |
| Cable Type | Armored - Single Loose Tube |
| Color | Putty white |
| Distribution Ports, quantity | 432 |
| Fibers per Feeder Cable, quantity | 24 |
| Interface, Input | SC |
| Interface Feature, Input | APC |
| Mounting | Pad |
| Splitter Slots, quantity | 24 |

Dimensions

| | |
|----------------|--------------------|
| Height | 1,066.8 mm 42 in |
| Width | 685.8 mm 27 in |
| Depth | 457.2 mm 18 in |
| Cable Length | 30.48 m 100 ft |
| Enclosure Size | Medium |

Material Specifications

| | |
|---------------|---------------|
| Finish | Powder coated |
| Material Type | Aluminum |

FD3-AG144J00GBBP2

Environmental Specifications

Environmental Space Above ground

Packaging and Weights

Packaging quantity 1

Packaging Type Pallet

Regulatory Compliance/Certifications

| Agency | Classification |
|------------|--|
| CHINA-ROHS | Above maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant/Exempted |
| UK-ROHS | Compliant/Exempted |

