

# FD3-AG288J2AJBBP2



FDH 3000 Fiber Distribution Medium Cabinet, 288F, SC/APC, (2) 32-splitter modules, dielectric loose tube, 100 ft, 24F

## Product Classification

Regional Availability	North America
Product Type	Fiber distribution hub
Product Series	FDH 3000

## General Specifications

Access	Front
Cable Type	Dielectric - Loose Tube
Color	Putty white
Distribution Ports, quantity	432
Fibers per Feeder Cable, quantity	24
Interface, Input	SC
Interface Feature, Input	APC
Mounting	Pad
Split Ratio	Symmetrical
Splitter Slots, quantity	24
Splitter Type	1 x 32
Splitter, quantity	2

## Dimensions

Height	1,066.8 mm   42 in
Width	685.8 mm   27 in
Depth	457.2 mm   18 in
Cable Length	30.48 m   100 ft
Enclosure Size	Medium

## Material Specifications

Finish	Powder coated
--------	---------------

# FD3-AG288J2AJBBP2

---

**Material Type** Aluminum

## Environmental Specifications

**Environmental Space** Above ground

## Packaging and Weights

**Packaging quantity** 1

**Packaging Type** Pallet

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

