

# FD3-AG360J00GDBP1



FDH 3000 Fiber Distribution Medium Cabinet, 360F, SC/APC, no splitters, single armor loose tube, 100 ft, 12F

## Product Classification

Regional Availability	North America
Product Type	Fiber distribution hub
Product Series	FDH 3000

## General Specifications

Access	Front
Cable Type	Armored - Single Loose Tube
Color	Putty white
Distribution Cables, quantity	3
Distribution Ports, quantity	432
Fibers per Feeder Cable, quantity	12
Interface, Input	SC
Interface Feature, Input	APC
Mounting	Pad
Splitter Slots, quantity	24

## Dimensions

Height	1,066.8 mm   42 in
Width	685.8 mm   27 in
Depth	457.2 mm   18 in
Cable Length	30.48 m   100 ft
Enclosure Size	Medium

## Material Specifications

Finish	Powder coated
Material Type	Aluminum

# FD3-AG360J00GDBP1

---

## Environmental Specifications

**Environmental Space** Above ground

## Packaging and Weights

**Packaging quantity** 1

**Packaging Type** Pallet

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

