FD3-AG432J00U20P2



FDH 3000 Fiber Distribution Medium In-Hub Splice Cabinet, 432F, SC /APC, O splitters, LT pigtails, heat-shrink fusion, 24F

Product Classification

Regional Availability	North America	
Product Type	Fiber distribution hub	
Product Series	FDH 3000	
General Specifications		
Access	Front	
Cable Type	Pigtails - Loose Tube	
Color	Putty white	
Distribution Cables, quantity	0	
Distribution Ports, quantity	432	
Fibers per Feeder Cable, quantity	24	
Interface, Input	SC	
Interface Feature, Input	APC	
Mounting	Pad	
Splitter Slots, quantity	24	
Dimensions		
Height	1,066.8 mm 42 in	
Width	685.8 mm 27 in	
Depth	457.2 mm 18 in	
Cable Length	30.48 m 100 ft	
Enclosure Size	Medium	
Material Specifications		
Finish	Powder coated	
Material Type	Aluminum	

Page 1 of 2

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: February 6, 2025



FD3-AG432J00U20P2

Environmental Specifications

Environmental Space	Above ground	
Packaging and V	Veights	
Packaging quantity	1	
Packaging Type	Pallet	
Regulatory Compliance/Certifications		
Agency	Classification	
CHINA-ROHS	Above maximum concentration value	

CHINA ROLIS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



Page 2 of 2

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: February 6, 2025

