FD3-AG432J00U20P4



FDH 3000 Fiber Distribution Medium In-Hub Splice Cabinet, 432F, SC /APC, O splitters, LT pigtails, heat-shrink fusion, 48F

Product Classification

Regional Availability North America

Product Type Fiber distribution hub

Product Series FDH 3000

General Specifications

Access Front

Cable TypePigtails - Loose Tube

Color Putty white

Distribution Cables, quantity 0

Distribution Ports, quantity 432

Fibers per Feeder Cable, quantity 48

Interface, Input SC

Interface Feature, Input APC

Mounting Pad

Splitter Slots, quantity 24

Dimensions

Height 1,066.8 mm | 42 in

Width 685.8 mm | 27 in

Depth 457.2 mm | 18 in

Enclosure Size Medium

Material Specifications

Finish Powder coated

Material Type Aluminum



FD3-AG432J00U20P4

Environmental Specifications

Environmental Space Above ground

Packaging and Weights

Packaging quantity

Packaging Type Pallet

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

