FD3-AG432J1ATCBP4



FDH 3000 Fiber Distribution Medium Cabinet, 432F, SC/APC, 32-splitter module, dielectric ribbon, 100 ft, 48F

Product Classification

Regional Availability North America

Product Type Fiber distribution hub

Product Series FDH 3000

General Specifications

Access Front

Cable TypeDielectric - Ribbon

Color Putty white

Distribution Cables, quantity 2

Distribution Ports, quantity 432

Fibers per Distribution Cable, quantity 216

Fibers per Feeder Cable, quantity 48

Interface, Input SC

Interface Feature, Input APC

Mounting Pad

Split Ratio Symmetrical

Splitter Slots, quantity 24

Splitter Type 1 x 32

Splitter, quantity 1

Dimensions

Height 1,066.8 mm | 42 in

Width 686 mm | 27.008 in

Depth 457 mm | 17.992 in

Cable Length 30.48 m | 100 ft

Enclosure Size Medium

COMMSC PE®

FD3-AG432J1ATCBP4

Material Specifications

Finish Powder coated

Material Type Aluminum

Environmental Specifications

Environmental Space Above ground

Packaging and Weights

Packaging quantity

Packaging Type Pallet

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

