FD3-AJ288J00JBBP4



FDH 3000 Fiber Distribution Large Cabinet, 288F, SC/APC, no splitters, dielectric loose tube, 100 ft, 48F

Product Classification

Regional Availability North America

Product Type Fiber distribution hub

Product Series FDH 3000

General Specifications

Access Front and rear door

Cable TypeDielectric - Loose Tube

Color Putty white

Distribution Cables, quantity 2

Distribution Ports, quantity 288

Fibers per Distribution Cable, quantity 144

Fibers per Feeder Cable, quantity 48

Interface, Input SC

Interface Feature, Input APC

Mounting Pad

Dimensions

Height 1,238.25 mm | 48.75 in

Width 1,220.47 mm | 48.05 in

Depth 497.33 mm | 19.58 in

Cable Length 30.48 m | 100 ft

Enclosure Size Large

Material Specifications

Finish Powder coated

Material Type Aluminum

COMMSCOPE®

FD3-AJ288J00JBBP4

Environmental Specifications

Environmental Space Above ground

Packaging and Weights

Packaging quantity

Packaging Type Pallet

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

