


FD3-AJ864J2TPFBP5X



FDH 3000 Large PFP cabinet, 864-Pos, SC/APC, two (2) 1x32 Custom Splitters, Dry-Dry Single Armor Ribbon OSP, 100ft, 288f. Feeder, (2) 432f. Distribution, 48.74"H* x 47.39"W x 19.58"D *Includes 6" tall riser

Product Classification

Regional Availability	North America
Product Type	Fiber distribution hub
Product Series	FDH 3000

General Specifications

Access	Front Rear
Cable Type	Armored - Ribbon
Distribution Cables, quantity	2
Distribution Ports, quantity	864
Fibers per Distribution Cable, quantity	432
Fibers per Feeder Cable, quantity	288
Mounting	Pad
Splitter Type	1 x 32
Splitter, quantity	2

Dimensions

Height	1238 mm 48.74 in
Width	1,203.71 mm 47.39 in
Depth	497.33 mm 19.58 in
Cable Length	30.48 m 100 ft
Enclosure Size	Large

Material Specifications

Finish	Powder coated
Material Type	Steel

FD3-AJ864J2TPFBP5X

Environmental Specifications

Environmental Space Above ground

Packaging and Weights

Packaging quantity 1

Packaging Type Pallet