

# FD3-AR036J00M00P8



Mini FDH 3000 Fiber Distribution Hub, 72-fiber shell, 36 fibers loaded, SC /APC, distribution patch, feeder pigtailed

## Product Classification

|                              |                        |
|------------------------------|------------------------|
| <b>Regional Availability</b> | North America          |
| <b>Product Type</b>          | Fiber distribution hub |
| <b>Product Series</b>        | FDH 3000               |
| <b>Warranty</b>              | One year               |

## General Specifications

|  |             |
|--|-------------|
| <b>Access</b>                                  | Front       |
| <b>Color</b>                                   | Putty white |
| <b>Distribution Cables, quantity</b>           | 3           |
| <b>Distribution Ports, quantity</b>            | 72          |
| <b>Fibers per Distribution Cable, quantity</b> | 12          |
| <b>Fibers per Feeder Cable, quantity</b>       | 8           |
| <b>Interface, Input</b>                        | SC          |
| <b>Interface Feature, Input</b>                | APC         |
| <b>Mounting</b>                                | Pole   Wall |
| <b>Splitter Slots, quantity</b>                | 4           |

## Dimensions

|                       |                  |
|-----------------------|------------------|
| <b>Height</b>         | 482.6 mm   19 in |
| <b>Width</b>          | 330.2 mm   13 in |
| <b>Depth</b>          | 203.2 mm   8 in  |
| <b>Enclosure Size</b> | Mini             |

## Material Specifications

|                      |               |
|----------------------|---------------|
| <b>Finish</b>        | Powder coated |
| <b>Material Type</b> | Aluminum      |

# FD3-AR036J00M00P8

---

## Environmental Specifications

|                                |   |
|--------------------------------|---|
| <b>Environmental Space</b>     | Aerial  |
| <b>Qualification Standards</b> | Telcordia GR-3123-CORE   Telcordia GR-3125-CORE |

## Packaging and Weights

|                           |        |
|---------------------------|--------|
| <b>Packaging quantity</b> | 1      |
| <b>Packaging Type</b>     | Pallet |

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| CHINA-ROHS    | Above maximum concentration value  |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant/Exempted   |
| UK-ROHS       | Compliant/Exempted   |



## \* Footnotes

|                 |  |
|-----------------|--|
| <b>Warranty</b> | For more information, please consult our Product Warranty guidelines |
|-----------------|--|