

FD3-PA096J00M4210



FDH 3000 Fiber Distribution Hub in a Pedestal, 96F, SC/APC, no splitters, ribbon pigtails, 96 splice cap., 6F spliced feeder

- Metal cabinet and can be placed in the ground without pouring a concrete pad or installing a hand hole
- Typically deployed for neighborhoods of 144 homes or higher
- Features full size trays for splicing incoming feeder and outgoing distribution cables and the option of adding hardened drop connections
- Modeled after the FDH 3000 fiber distribution hubs

Product Classification

Regional Availability	North America
Product Type	Hub in a pedestal
Product Series	FDH 3000

General Specifications

Access	Front
Cable Type	Pigtails - Ribbon
Color	Putty white
Distribution Ports, quantity	96
Fibers per Feeder Cable, quantity	6
Interface, Input	SC
Interface Feature, Input	APC
Mounting	Pedestal
Splice Tray Included, quantity	4
Splice Tray Type Included	24-way, heat shrink
Splicing Capacity, maximum	96
Splitter Slots, quantity	6

Dimensions

Enclosure Size	Small
-----------------------	-------

Material Specifications

Finish	Powder coated
---------------	---------------

FD3-PA096J00M4210

Material Type Molded plastic

Environmental Specifications

Environmental Space Above ground

Packaging and Weights

Included Cable clamps (2)

Packaging quantity 1

Packaging Type Pallet

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

