

# FD3-PA096J00U4410



FDH 3000 Fiber Distribution Hub in a Pedestal, 96F, SC/APC, no splitters, stranded pigtails, 96 splice cap., 6F feeder

- Metal cabinet and can be placed in the ground without pouring a concrete pad or installing a hand hole
- Typically deployed for neighborhoods of 144 homes or higher
- Features full size trays for splicing incoming feeder and outgoing distribution cables and the option of adding hardened drop connections
- Modeled after the FDH 3000 fiber distribution hubs

## Product Classification

|                              |                   |
|------------------------------|-------------------|
| <b>Regional Availability</b> | North America     |
| <b>Product Type</b>          | Hub in a pedestal |
| <b>Product Series</b>        | FDH 3000          |

## General Specifications

|  |                     |
|--|---------------------|
| <b>Access</b>                                  | Front   Rear        |
| <b>Cable Type</b>                              | Pigtails - Stranded |
| <b>Color</b>                                   | Green               |
| <b>Distribution Cables, quantity</b>           | 8                   |
| <b>Distribution Ports, quantity</b>            | 96                  |
| <b>Fibers per Distribution Cable, quantity</b> | 12                  |
| <b>Fibers per Feeder Cable, quantity</b>       | 6                   |
| <b>Interface, Input</b>                        | SC                  |
| <b>Interface Feature, Input</b>                | APC                 |
| <b>Mounting</b>                                | Pad                 |
| <b>Splice Tray Included, quantity</b>          | 4                   |
| <b>Splice Tray Type Included</b>               | 24-way, heat shrink |
| <b>Splicing Capacity, maximum</b>              | 96                  |
| <b>Splitter Slots, quantity</b>                | 6                   |

## Dimensions

|               |                    |
|---------------|--------------------|
| <b>Height</b> | 889 mm   35 in     |
| <b>Width</b>  | 292.1 mm   11.5 in |

# FD3-PA096J00U4410

---

**Depth** 368.3 mm | 14.5 in

**Enclosure Size** Small

## Material Specifications

**Material Type** Steel

## Environmental Specifications

**Environmental Space** Above ground

## Packaging and Weights

**Included** Cable clamps (4)

**Packaging quantity** 1

**Packaging Type** Pallet

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| CHINA-ROHS    | Above maximum concentration value  |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant/Exempted   |
| UK-ROHS       | Compliant/Exempted   |

