



Unshielded Recessed Angled Discrete Distribution Module Panel, SL, 1U, 24 port, Black

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	RJ45 patch panel
Product Series	SL Series

General Specifications

Cable Type	Unshielded
Color	Black
Modules, quantity	0
Panel Style	Angled recessed
Rack Type	EIA 19 in
Rack Units	1
Total Ports, quantity	24

Dimensions

Height	44.45 mm 1.75 in
Width	482.6 mm 19 in
Depth, with cable management	137.16 mm 5.4 in

Material Specifications

Material Type	High-impact, flame retardant, thermoplastic Powder-coated steel
----------------------	---

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Flammability Rating	UL 94 V-0

760237044 | CPPR-UDDM-SL-1U-24

Safety Standard

RCM | UL | cUL

Packaging and Weights

Packaging Material

Eco-friendly, single-use plastics-free

Packaging quantity

1

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

